LEGEND:

ISOLATION VALVE

BYPASS VALVE


PRESSURE GAUGE &
SAMPLE POINT

OPEN DRAIN

VACUUM BREAKER
RAW WATER LINES


FILTERED WATER LINES

► WATER TO OPEN DRAIN



Τ	DNX Series Quadplex	Typical	Peak	RO		Pipe Size		Media	Mineral Tank		Installation			Chinatan	0
		Max.System Recommended Flow Rates			Max Flow To Drain	Service	Drain	Per Tank	Diameter	Height	Height	Depth	Width	Shipping Weight	Operating Weight
ı	Model	USGPM	USGPM	USGPM	USGPM	in	in	CF	in	in	in	in	in	lbs	lbs
ı		I/s	I/s	I/s	I/s	mm	mm	(m³)	mm	mm	mm	mm	mm	kg	kg
Γ	DNX 30-2"	192.0	292.0	39.0	60.0	2"	2"	12.5	30	72	104	45	144	6,400	12,800
ı		12.1	18.4	2.5	3.8	50	50	0.35	762	1,829	2,642	1,143	3,658	2,904	5,808
J	DNX 36-3"	276.0	420.0	57.0	85.0	3"	3"	17.6	36	72	105	51	168	8,400	16,400
1		17.4	26.5	3.6	5.4	75	75	0.50	914	1,829	2,667	1,295	4,267	3,811	7,441
Γ	DNX 42-3'	384.0	576.0	77.0	120.0	3"	3"	24.0	42	72	113	65	192	11,200	24,800
l		24.2	36.3	4.9	7.6	75	75	0.68	1,067	1,829	2,870	1,651	4,877	5,082	11,252
Γ	DNX 48-4"	504.0	752.0	100.0	160.0	4"	4"	31.0	48	72	115	71	216	14,312	31,512
1		31.8	47.4	6.3	10.1	100	100	0.88	1,219	1,829	2,921	1,803	5,486	6,494	14,298

Typical service based on 10 usgpm/ft² Peak based on 15 usgpm/ft² Flowrates may change depending upon actual feed water quality water condition Backwash flowrates based on cold water. If regeneration feed water is above 45%, The backwash flow rate will have to be increased.



NOTES

-MAXIMUM RECOMMENDED SYSTEM PRESSURE IS 100 PSIG (690 kPa).
-MAXIMUM RECOMMENDED SYSTEM TEMPERATURE IS 90° F (32°C).
-TANKS, AND MEDIA ARE NSF APPROVED. TRIPOD TANKS TO BE SECURELY ATTACHED TO THE FLOOR.

-ALL PIPING, FITTINGS, INTERCONNECTING PIPING, ISOLATION & SAMPLE VALVES AND GAUGES SHOWN BY BROKEN LINES ARE BY OTHERS -SUPPLIED MANIFOLD IS SCH 80 PVC AND IS SUPPLIED WITH ONE VACUUM BREAKER. RECOMMENDED AIR RELEASE VALVE IS BY OTHERS. SYSTEM CAN BE PIPED AS RAW WATER OR TREATED WATER REGENERATION. -ALL PIPING MUST BE PROPERLY SUPPORTED AND BRACE TO HANDLE THE THRUST OF THE CHANGE OF WATER FLOW (BY OTHERS)

-GLASS FIBER REINFORCED THERMOPLASTIC DIAPHRAGM VALVES ARE SEQUENCED BY AN ELECTRONIC MULTIPORT STAGER. ELECTRICAL POWER REQUIRED - 120 VOLT, 1 PHASE, 60 Hz. MULTI-TANK SYSTEMS ARE SERIES REGENERATION. -SYSTEM MUST BE INSTALLED TO COMPLY WITH ALL FEDERAL, STATE, PROVINCIAL AND LOCAL CODES.

-FLOOR DRAINS MUST BE SIZED TO CARRY THE MAXIMUM LISTED FLOW TO DRAIN. -REFER TO THE INSTALLATION AND OPERATION MANUAL FOR FURTHER DETAILS.

-MEDIA BED CONSISTS OF NSF APPROVED, NEXTSAND ON A GRADED SUPPORT BED

Canature WaterGroup Commercial/Industrial Engineering Division

DNX SERIES NEXTSAND QUADRAPLEX FILTER SYSTEM

THIS DOCUMENT CONTAINS INFORMATION WHICH IS PROPRIETARY TO CANATURE WATERGROUP. THE REPRODUCTION, TRANSFER, OR OTHER EXPLOITATION OF ANY INFORMATION CONTAINED HEREIN IS NOT PERMITTED WITHOUT PRIOR WRITTEN APPROVAL OF CANATURE WATERGROUP. THE MANUFACTURER RESERVES THE RIGHT TO MAKE PRODUCT REVISIONS, WHICH MAY DEVIATE FROM THE SPECIFICATIONS AND DESCRIPTIONS STATED HEREIN WITHOUT OBLIGATION TO CHANGE PREVIOUSLY MANUFACTURED PRODUCTS OR TO NOTE THE CHANGE.

Project	Date	6/30/17	Rev
	Dwg#	DNX 04	0